




MAESTRO

Version 2025-12

Overall dimensions



	05.07.05	07.10.07	09.12.08	09.15.08	09.20.08
X	500 (19.69)	700 (27.56)	900 (35.43)	900 (35.43)	900 (35.43)
Y	700 (27.56)	1000 (39.37)	1200 (47.24)	1500 (59.06)	2000 (78.74)
Z	500 (19.69)	660 (25.98)	800 (31.50)	800 (31.50)	800 (31.50)
LX	1018 (40.08)	1218 (47.95)	1510 (59.45)	1510 (59.45)	1510 (59.45)
LX1	66 (2.60)	66 (2.60)	68 (2.68)	68 (2.68)	68 (2.68)
LX2	60 (2.36)	60 (2.36)	69 (2.72)	69 (2.72)	69 (2.72)
LY	1707 (67.20)	2104 (82.83)	2483 (97.76)	2783 (109.57)	3283 (129.25)
LY1	194 (7.64)	194 (7.64)	191 (7.52)	191 (7.52)	191 (7.52)
LY2	263 (10.35)	260 (10.24)	262 (10.31)	262 (10.31)	262 (10.31)
LZ	2315 (91.14)	2634 (103.70)	2954 (116.30)	2954 (116.30)	2954 (116.30)
LZ1	618 (24.33)	777 (30.59)	934 (36.77)	934 (36.77)	934 (36.77)
LZ2 ²⁾	107 (4.21)	107 (4.21)	141 (5.55)	141 (5.55)	141 (5.55)
LZ3	1616 (63.62)	1776 (69.92)	1919 (75.55)	1919 (75.55)	1919 (75.55)
PH	700 (27.56)	700 (27.56)	600 (23.62)	600 (23.62)	600 (23.62)
PY	1250 (49.21)	1650 (64.96)	2030 (79.92)	2330 (91.73)	2830 (111.42)
PY1	90 (3.54)	150 (5.91)	201 (7.91)	201 (7.91)	201 (7.91)
Max. part weight	250 (551.16)	900 (1984.16)	1300 (2866)	1500 (3306.93)	1800 (3968.32)
CMM weight approx.	900 (1984.16)	1400 (3086.47)	2350 (5180.86)	2600 (5732.01)	3000 (6613.86)


Dimensions in mm (in) and weight in kg (lb)

1) With bellows LX = LX + 6 mm (+0,23 in)

2) Sensor interface included

Technical characteristics

Mechanical frame		X: Micromachined anodized light alloy extrusion Y: Integral dovetail guideways, machined into the table Z: Micromachined anodized light alloy extrusion
Surface plate		Material: Granite Flatness: according to DIN 876/III M8 x 1.25 threaded inserts thread length 20 mm Diagonally staggered hole pattern: MAESTRO 05.07.05: X = 300 mm (11.81 in) ; Y = 300 mm (11.81 in) MAESTRO 07.10.07: X = 300 mm (11.81 in) ; Y = 300 mm (11.81 in) MAESTRO 09.YY.08: X = 350 mm (13.78 in) ; Y = 350 mm (13.78 in)
Sliding system		Air bearings on all axes
Measuring system		METALLUR® linear scales; overall system resolution: 0.0003 µm
Temperature compensation		Extended temperature 16 - 26 °C (61 °F - 79 °F): Multi-sensor technology
Ram counterbalance		Pneumatic, adjustable
Controller		Embedded and located at the rear side of the system
Electrical power	Supply voltage Consumption	100-120/220-240 V ± 10 % - 50/60 Hz Constant: < 0.5 kVA; Peak: 1.5 kVA
Air supply	Pressure Consumption	≥ 0.5 MPa (5 bar) class 4, according to ISO 8573/1 < 70 NI/min (for 05.07.05 and 07.10.07 sizes); < 90 NI/min (for 09.YY.08 size) UNI ISO 8778 Air consumption in Standby with EcoMode+ : 0NL/min
Operating specifications		Ambient temperature: 10 - 40 °C (50 °F - 104 °F) Relative humidity: 20 % - 90 %, non-condensing



Minimum door opening requirements

Machine maximum overall dimension			
	Standard size frames	Width mm (in) ¹⁾	Height mm (in) ¹⁾
In case of front lift	05.07.05	1019 (40.12)	1860 (73.23)
	07.10.07 – 07.15.07	1219 (47.99)	2050 (80.71)
	09.12.08 – 09.15.08 – 09.20.08	1564 (61.58)	2151 (84.69)
In case of lateral lift	09.12.08	2533 (99.72)	2151 (84.69)
	09.15.08	2833 (111.54)	2151 (84.69)
	09.20.08	3333 (131.22)	2151 (84.69)

- 1) Minimum dimensions are listed:
 w/o CMM Z cover for MAESTRO 05.07.05 and MAESTRO 07.10.07
 w/o pedestals and CMM Z cover for MAESTRO 09.YY.08
 Dimensions shown are from the highest point at the top of the CMM to the lowest point on the CMM as in shipped condition.
 Dimensions shown do not include lifting equipment.
 Dimensions shown are with 25 mm (0.98 in) minimum clearance all around.
 NOTE: For detailed information on how to handle the CMM movement please refer to transport and installation instructions.

MAESTRO basic configuration: Specifications with articulating wrist

ISO 10360-2:2009

Max. permissible errors (MPE) and limits (MPL) [μm]		05.07.05	07.10.07	09.YY.08
Volumetric length measurement error 18 - 22 °C (64 °F - 71 °F)	E0/E150	1.5 + L/350	1.5 + L/350	1.5 + L/350
Volumetric length measurement error 16 - 26 °C (61 °F - 79 °F)	E0/E150	1.5 + L/300	1.5 + L/300	1.5 + L/300
Repeatability range	R0	1.2	1.2	1.2

ISO 10360-5:2020

Max. permissible errors MPE [μm]		05.07.05	07.10.07	09.YY.08
Scanning mode form error	P _{Form.Sph.Scan:PP:Tact}	2.0	2.0	2.0
Scanning mode size error	P _{Size.Sph.Scan:PP:Tact}	2.0	2.0	2.0
Scanning time	τ _{Sph.Scan:PP:Tact}	35	35	35
Scanning mode form error - not pre-defined path	P _{Form.Sph.Scan:NPP:Tact}	2.0	2.0	2.0
Scanning mode size error - not pre-defined path	P _{Size.Sph.Scan:NPP:Tact}	2.0	2.0	2.0
Scanning time - not pre-defined path	τ _{Sph.Scan:NPP:Tact}	50	50	50
Single-stylus form error	P _{Form.Sph.1x25:SS:Tact}	1.5	1.5	1.5
Single-stylus size error	P _{Size.Sph.1x25:SS:Tact}	1.3	1.3	1.3
Multi-stylus form error	P _{Form.Sph.5x25:Emp:Tact}	5.9	5.9	5.9
Multi-stylus size error	P _{Size.Sph.5x25:Emp:Tact}	2.1	2.1	2.1
Multi-stylus location error	L _{Dia.5x25:Emp:Tact}	4.0	4.0	4.0
Scanning mode form error with FastCal	P _{Form.Sph.Scan:PP:Tact}	4.5	4.5	4.5
Scanning mode size error with FastCal	P _{Size.Sph.Scan:PP:Tact}	4.0	4.0	4.0
Scanning time with FastCal	τ _{Sph.Scan:PP:Tact}	35	35	35
Scanning mode form error - not pre-defined path with FastCal	P _{Form.Sph.Scan:NPP:Tact}	4.5	4.5	4.5
Scanning mode size error - not pre-defined path with FastCal	P _{Size.Sph.Scan:NPP:Tact}	4.0	4.0	4.0
Scanning time - not pre-defined path with FastCal	τ _{Sph.Scan:NPP:Tact}	50	50	50
Multi-stylus form error with FastCal	P _{Form.Sph.5x25:Inf:Tact}	11.0	11.0	11.0
Multi-stylus size error with FastCal	P _{Size.Sph.5x25:Inf:Tact}	3.5	3.5	3.5
Multi-stylus location error with FastCal	L _{Dia.5x25:Inf:Tact}	9.5	9.5	9.5

- E0, R0 are valid for DST 200: styli ø 3 x 50 mm (SS) and DTT 30 module: ø 3 x 30 mm (TC). Length unit measure (L) in mm.
- All ISO 10360-5 specification are valid for DST 200: styli ø 3 x 50mm (SS) and ø 5 x 20 mm (SS) and DTT 30 module: ø 3 x 30 mm (TC) and ø 4 x 20 mm (SS) without extension; anywhere in the measuring volume.
- ISO 10360-5 specifications are valid for a test sphere with calibrated form ≤ 0.1 μm and the respective uncertainty ≤ 0.1 μm and uncertainty of calibrated sphere diameter ≤ 0.21 μm.
- Multi-stylus error test performed up to 100 mm from the qualification sphere.

MAESTRO configuration with Accuracy+ and Throughput+ options: Specifications with articulating wrist

ISO 10360-2:2009

Max. permissible errors (MPE) and limits (MPL) [μm]		05.07.05	07.10.07	09.YY.08
Volumetric length measurement error 18 - 22 °C (64 °F - 71 °F)	E0/E150	1.2 + L/350	1.2 + L/350	1.2 + L/350
Volumetric length measurement error 16 - 26 °C (61 °F - 79 °F)	E0/E150	1.2 + L/300	1.2 + L/300	1.2 + L/300
Repeatability range	R0	1.0	1.0	1.0

ISO 10360-5:2020

Max. permissible errors MPE [μm]		05.07.05	07.10.07	09.YY.08
Scanning mode form error	P _{Form.Sph.Scan:PP:Tact}	1.8	1.8	1.8
Scanning mode size error	P _{Size.Sph.Scan:PP:Tact}	1.8	1.8	1.8
Scanning time	$\tau_{\text{Sph.Scan:PP:Tact}}$	20	20	20
Scanning mode form error - not pre-defined path	P _{Form.Sph.Scan:NPP:Tact}	1.8	1.8	1.8
Scanning mode size error - not pre-defined path	P _{Size.Sph.Scan:NPP:Tact}	1.8	1.8	1.8
Scanning time - not pre-defined path	$\tau_{\text{Sph.Scan:NPP:Tact}}$	30	30	30
Single-stylus form error	P _{Form.Sph.1x25:SS:Tact}	1.2	1.2	1.2
Single-stylus size error	P _{Size.Sph.1x25:SS:Tact}	1.0	1.0	1.0
Multi-stylus form error	P _{Form.Sph.5x25:Emp:Tact}	4.9	4.9	4.9
Multi-stylus size error	P _{Size.Sph.5x25:Emp:Tact}	1.5	1.5	1.5
Multi-stylus location error	L _{Dia.5x25:Emp:Tact}	3.5	3.5	3.5
Scanning mode form error with FastCal	P _{Form.Sph.Scan:PP:Tact}	4.5	4.5	4.5
Scanning mode size error with FastCal	P _{Size.Sph.Scan:PP:Tact}	4.0	4.0	4.0
Scanning time with FastCal	$\tau_{\text{Sph.Scan:PP:Tact}}$	30	30	30
Scanning mode form error - not pre-defined path with FastCal	P _{Form.Sph.Scan:NPP:Tact}	4.5	4.5	4.5
Scanning mode size error - not pre-defined path with FastCal	P _{Size.Sph.Scan:NPP:Tact}	4.0	4.0	4.0
Scanning time - not pre-defined path with FastCal	$\tau_{\text{Sph.Scan:NPP:Tact}}$	45	45	45
Multi-stylus form error with FastCal	P _{Form.Sph.5x25:Inf:Tact}	11.0	11.0	11.0
Multi-stylus size error with FastCal	P _{Size.Sph.5x25:Inf:Tact}	3.5	3.5	3.5
Multi-stylus location error with FastCal	L _{Dia.5x25:Inf:Tact}	9.5	9.5	9.5

- E0, R0 are valid for DST 200: styli $\varnothing 3 \times 50$ mm (SS) and DTT 30 module: $\varnothing 3 \times 30$ mm (TC). Length unit measure (L) in mm.
- All ISO 10360-5 specification are valid for DST 200: styli $\varnothing 3 \times 50$ mm (SS) and $\varnothing 5 \times 20$ mm (SS) and DTT 30 module: $\varnothing 3 \times 30$ mm (TC) and $\varnothing 4 \times 20$ mm (SS) without extension; anywhere in the measuring volume.
- ISO 10360-5 specifications are valid for a test sphere with calibrated form $\leq 0.1 \mu\text{m}$ and the respective uncertainty $\leq 0.1 \mu\text{m}$ and uncertainty of calibrated sphere diameter $\leq 0.21 \mu\text{m}$.
- Multi-stylus error test performed up to 100 mm from the qualification sphere.

Non-contact sensors specifications

Max. permissible errors (MPE) and limits (MPL) [µm]				DSL 100 ¹⁾
ISO 10360-8:2013	Sphere	Probing dispersion value	P _{Form.Sph.D95%:Tr:ODS}	12
	Sphere	Probing form error	P _{Form.Sph.1x25:Tr:ODS}	8
	Sphere	Probing size error All	P _{Size.Sph.All:Tr:ODS}	14
	Sphere	Articulated location value	L _{Dia.5x25:Art:ODS}	24
	Plane	Probing dispersion value	P _{Form.Pla.D95%:Tr:ODS}	15
ISO 10360-9:2013 ²⁾	Sphere	Probing location error	L _{Dia.2x25:MPS}	18

1) Some restrictions to workpiece size and machine configuration may apply when used on MAESTRO 05.07.05

2) DTT 100: stylus Ø 3 x 30 mm (TC) or DST 200: stylus Ø 3 x 50 mm (SS)

Specifications include measurement uncertainty according to ISO/TS 17865:2016 and are valid for:

- Constant CMM scanning speed of 25 mm/sec.
- Tests performed with standard configuration without (e.g. angular) adaptors or/and extensions.
- Exposure setting of 22 % (UD).
- Decimation setting of 100 % (if applicable).
- Automatic probe exchange when applicable for the test.
- Combination of DSL 100 with tactile probing sensor using the same styli specified for the single probing error test according to ISO 13060-5 when applicable for the test.
- Probing error test on spherical artifact performed on white matt sphere (properties according to PN: H00044223):
Calibrated for form with three great circles and maximum form deviation of 0.5 µm and maximum calibration uncertainty U of 0.04 µm
Calibrated for size with three great circles and maximum calibration uncertainty U of 0.02 µm.
- Probing error test on plane artifact performed on white plane (properties according to PN: H00044226) Calibrated for form with union jack strategy with approximately 3000 individual points with maximum form deviation of 1.5 µm and maximum calibration uncertainty U of 0.28 µm.

Throughput and dynamics

	Max. 3D speed	Max. 3D acceleration ⁴⁾
Dynamics	700 mm/s (27.56 in/s)	2800 mm/s ² (110.24 in/s ²)
Dynamics with Throughput+ option ³⁾	1100 mm/s (43.31 in/s)	6500 mm/s ² (255.91 in/s ²)

3) Dynamics reduction may apply to meet specific customer and/or local safety requirements.


4) Acceleration reduction may apply with pneumatic dampers configuration.

Temperature specifications


	Lab temperature	Extended temperature
Ambient temperature	18 °C - 22 °C (64 °F - 71 °F)	16 °C - 26 °C (61 °F - 79 °F)
Max. air temperature variation	1 K/h - 2 K/24h (1.8 °F/h - 3.6 °F/24h)	1 K/h - 5 K/24h (1.8 °F/h - 9 °F/24h)
Max. gradient in space	1 K/m (1.8 °F/m)	1 K/m (1.8 °F/m)

Probe heads and sensors


Technical characteristics	Digital wrist DW 2.5
Angular rotation	A axis: $\pm 105^\circ$ B axis: infinite rotation motion
Angular rotation step	2.5°
Max. applied torque	1.2 Nm
Max. extensions length	450 mm (17.72 in)




Technical characteristics	Digital touch trigger probe DTT
Probe connector	M8 with active 1 wire connection
Probing direction	6 Way $\pm X$, $\pm Y$ and $\pm Z$
Stylus mounting	M2 thread
Max. straight styli length	Up to 75 mm (2.95 in) with any material or 100 mm (3.94 in) with carbon fiber (probe module DTT 100)
Max. star styli dimensions	Up to length: 50 mm (1.97 in); extension: 20 mm (0.79 in); span: 30 mm (1.18 in) (probe module DTT 100)
Min. styli diameter ball	Smallest Styli ball 0.3mm (probe module DTT 30)



Technical characteristics	Digital scanning probe DST 200
Probe connector	TKJ (kinematic joint)
Measuring range	± 2 mm (0.08 in) in all axes
Stylus holder thread	M3
Max. stylus weight (including stylus clamping)	33 g (0.07 lb)
Max. stylus length	Axial: up to 225 mm (8.86 in) Lateral: up to 100 mm (3.94 in)



Technical characteristics	Digital laser scanner DSL 100
Laser class	2 (EN / IEC 60825-1:2014)
Standoff and depth (Z)	90 ± 30 mm (3.54 ± 1.18 in) (additional 30 mm (1.18 in) with eFOV2)*
Laser line width	80 mm (3.15 in) (at mid-field)
Scanning frequency (lines per second)	300 Hz
Data rate	600 000 pts/sec
Protection against dust and water	IP51 (IEC/EN 60529) (except for warm-up terminal)
Weight	427 g (0.94 lb)




Dimensions in mm (in) and weights in g (lb)

* Points are collected even in the extended field of view (another 30 mm (1.18 in)) but with decreasing accuracy.


Performance verification

ISO 10360-2 Volumetric length measurement error E0




5 length gauges have to be measured 3 times with one probing at each end, in 7 different directions. All measurement results must be within MPE (E0).

ISO 10360-2 Volumetric length measurement error E150




5 length gauges have to be measured 3 times in the YZ or XZ plane with opposite styli, mounted 150 mm off the Z spindle axis.

ISO 10360-2 Repeatability range of the length measurement error



Extreme value of the repeatability range of the length measurement error, calculated by 3 repeated measurements on each size for a total of 35 values. The 35 repeatability range results must be within MPL (R0).

ISO 10360-5 Single-stylus form/size error



A precision sphere has to be measured with 25 probings.

$P_{\text{Form.Sph.1x25:SS:Tact}}$ is the range of all radii.
 $P_{\text{Form.Sph.1x25:SS:Tact}} = R_{\text{max}} - R_{\text{min}} = \text{sphere form.}$

$P_{\text{Size.Sph.1x25:SS:Tact}}$ is the deviation of measured and calibrated sphere diameter.

$P_{\text{Size.Sph.1x25:SS:Tact}} = D_{\text{meas}} - D_{\text{cal}}$

ISO 10360-5 Scanning mode form/size error




A precision sphere has to be scanned with 4 defined lines.

$P_{\text{Form.Sph.Scan:PP:Tact}}$ is the range of all radii.
 $P_{\text{Form.Sph.Scan:PP:Tact}} = R_{\text{max}} - R_{\text{min}} = \text{sphere form, scanning.}$

$P_{\text{Size.Sph.Scan:PP:Tact}}$ is the deviation of measured and calibrated sphere diameter.


$P_{\text{Size.Sph.Scan:PP:Tact}} = D_{\text{meas}} - D_{\text{cal}}$

ISO 10360-5 Multi-stylus error



A sphere is measured with 5 stylus (fixed probe head) or with 1 stylus in 5 orientations (articulating wrist) with 5 x 25 probings. Form, size and location error over 125 points.

ISO 10360-8 Optical distance sensors form/size error




A sphere is measured with 25 optical probings.

$P_{\text{Form.Sph.1x25:Tr:ODS}}$ is the range of all radii.
 $P_{\text{Form.Sph.1x25:Tr:ODS}} = R_{\text{max}} - R_{\text{min}} = \text{sphere form.}$
 $P_{\text{Size.Sph.1x25:Tr:ODS}}$ is the deviation of measured and calibrated sphere diameter.

$P_{\text{Size.Sph.1x25:Tr:ODS}} = D_{\text{meas}} - D_{\text{cal}}$

ISO 10360-9 Multiple probing systems form/size/location error




A sphere is measured with contact and non-contact sensor, with 25 probings each. Form and size error over all 50 points. Location error $L_{\text{Dia.2x25:MPS}} = \text{space distance between both centre points.}$

For more information, please refer to the brochure:

Acceptance and reverification tests for coordinate measuring machines (CMMs) – According to ISO 10360.

Probe and sensor availability



MAESTRO frame sizes

05.07.05

X: 500 mm
Y: 700 mm
Z: 500 mm



07.10.07

X: 700 mm
Y: 1000 mm
Z: 700 mm



09.YY.08

X: 900 mm
Y: 1200 mm | 1500 mm | 2000 mm
Z: 800 mm



MAESTRO pre-configured packages

MAESTRO can be configured using pre-configured packages, or by configuring all components such as size, sensors, racks, software, and accessories, completely individually.

MAESTRO Touch+

General-purpose measurements of size features with highly repeatable touch trigger probing.



Digital touch trigger probe
DTT



Metrology software
PC-DMIS



MAESTRO Scan+

General-purpose measurements of size and form features with high performance tactile scanning.



Digital scanning probe
DST 200



Metrology software
PC-DMIS



Scan Pilot for improved
scanning performance

MAESTRO Speed

High-throughput measurements of complete part surfaces with high measuring point density.



Digital laser scanner
DSL 100



Metrology software
PC-DMIS



Scan Pilot for improved
scanning performance



Digital changer rack DR
including modules for
DSL 100



Hexagon is the global leader in measurement technologies. We provide the confidence that vital industries rely on to build, navigate, and innovate. From microns to Mars, our solutions ensure productivity, quality, safety, and sustainability in everything from manufacturing and construction to mining and autonomous systems.

Hexagon (Nasdaq Stockholm: HEXA B) has approximately 24,800 employees in 50 countries and net sales of approximately 5.4bn EUR.

Learn more at hexagon.com